huber

KISS 212B

Heating Bath with KISS-Controller, consisting of insulated stainless steel bath with stainless steel housing. Powerful pressure and suction pump made of industrial plastic material. Temperature range up to 200°C. Bath bridge with hole for cooling probe (e.g. for immersion cooler TC45-TC100E). With adjustable overtemperature protection according to DIN 12876.

NEW: KISS controller:

KISS combines state-of-the-art technology with simple operation and stylish design. Models with KISS controller are suitable for routine tasks in research and industry and are convincing as practice oriented basic equipment:

- * Large, bright OLED display
- * Simple operation with menu navigation
- * Simultaneous display of set point, internal temperature, Tmin and Tmax
- * Status displays for pump, cooling and heating
- * USB (Device) and RS232 interfaces
- * Overtemperature protection, Safety class 3 (FL)
- * Autostart function for power failure
- * 3 colour versions available: grey (standard), blue, red

Option: Pt100 sensor connection #10688 to display (not control) e.g. of the process temperature (only available factory fitted, additional charge).

3-2-2 warranty - registration required.

Technical data according to DIN 12876

25...200 °C Operating temperature range with water cooling 20...200 °C with refrigerator -30...200 °C Temperature stability at 70°C 0.05 K temperature set point / display digital Absolute accuracy setup for calibration Internal temperature sensor Pt100 Alarm message optic, acoustic Safety classification Class III / FL 2,1 kW Heating power at 240V Heating power at 230V 2 kW Heating power at 220V 1,8 kW Heating power at 208V 1.6 kW Heating power at 200V 1,5 kW max. delivery 14 l/min 0.25 bar max. delivery pressure 10,5 l/min max. delivery (suction) max. delivery pressure (suction) 0,17 bar Pump connenction (optional) M16x1 male Bath volume 12 I

Order-No.: 2057.0004.98

Net weight

Filling capacity

Height of bath opening

Power supply requirement

Overall dimensions WxDxH **

max. current
min. Fuse
max. Fuse
Degree of Protection
min. ambient temperature
max. ambient temperature

Width bath opening WxD/ bath depth

11 kg 200-240V 1~/2~ 50/60Hz 10 A

10 A 10A 16A IP20 5 °C 40 °C

12 I

205 mm

290x152/ 150 mm

350x375x375 mm

from Serial-No.: 1.0/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Technical data according to DIN 12876

Included Accessories:

bath bridge #19595, cover for bath bridge #40836

Optional accessories:

pump adaptor #19607, cooling coil #30564, drain valve #6839, hose connector NW8/NW12, nozzle #33288, test tube racks Typ 1-4, holder for immersion cooler TC45(E) - TC100(E) #14562, temperature control / - connection hoses, thermofluids, various bath cover, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and +3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer). It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

^{**} Please respect space requirements. See operating conditions at www.huber-online.com